UTC-WALL-MOUNT1E

VESA 75/100 mm

- Firmly fix to a solid wall
- Weight capacity up to 14 kg
- Material: Steel
- Tilt: 180° up and down
- Rotation: 270° for portrait or landscape viewing
- Lift: 130.5 mm
- For UTC-510/515/520/307/310/315





Step 1

Tighten the wall plate on the wall by using four screws.

Step 2

Tighten the wall mount device plate on the rear cover of UTC unit by using four screws into VESA holes.





Step 3

Take the UTC unit with wall mount device plate to slide into wall mount plate on the wall.



UTC-WALL-MOUNT2E

VESA 100/200 mm

- Flush fit without movement
- Weight capacity up to 35 kg
- Material: Steel
- Sits: 42.5 mm from the wall
- For UTC-532 only





Step 1

Tighten the wall plate on the wall by using six screws.

Step 2

Tighten the wall mount device plate on the rear cover of UTC unit by using four screws into VESA holes.



Step 3

Take the UTC unit with wall mount device plate to hang into wall mount plate on the wall.





UTC-WALL-MOUNT3E

VESA 75/100 mm

- Firmly fix to a solid wall
- Weight capacity up to 20 kg
- Material: Steel
- Sits: 27 mm from the wall
- For UTC-515/520/307/310/315/ 318/320





Step 1

Tighten the wall plate on the wall by using four screws.

Step 2

Tighten the wall mount device plate on the rear cover of UTC unit by using four screws into VESA holes.





Take the UTC unit with wall mount device plate to slide into wall mount plate on the wall.





AD\ANTECH UTC-Wall-Mount

All product specifications are subject to change without notice.

UTC-WALL-MOUNT4E

VESA 75 mm

- Handy and Convenient supporter
- Firmly fix to solid wall
- Material:Steel
- Weight capacity up to 20 kg
- For UTC-510/307/310





Step 1

Tighten the wall plate on the wall by using four screws.



Step 3

Take the UTC unit with wall mount device plate to slide into wall mount plate on the wall.



Step 2

Tighten the wall mount device plate on the rear cover of UTC unit by using four screws into VESA holes.



UTC-WALL-MOUNT5E

VESA 75 mm

- Firmly fix to a solid wall
- Weight capacity up to 20 kg
- Material: Steel
- Sits: 8 mm from the wall
- For UTC-510/307/310





Step 1

Tighten the wall plate on the wall by using four screws.

Step 2

Tighten the wall mount device plate on the rear cover of UTC unit by using four screws into VESA holes.





Step 3

Take the UTC unit with wall mount device plate to slide into wall mount plate on the wall.





All product specifications are subject to change without notice.

